




Substation - Copper T Connector - 90 Degrees

By Burndy
Catalog # [NSNT1329](#)

Substation Connectors



Features

- Type NSNT T-Connector for Copper Tube or Cable to Cable
- High copper alloy reversible T-Connector for joining a wide range of run and tap cables
- Designed for one-wrench installation
- S in Catalog Number supplied with Standard 3/8" Hardware

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Connection Combination	Tube to Cable
Conductor - Copper Solid Tap Range	5 AWG-4/0 AWG
Conductor - Copper Solid Tap	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Type	• CU C Str-Run • CU C Solid-Run • CU C Str-Tap • CU C Solid-Tap • CU Tube Std-Run
Conductor - Copper Str Tap Range	6 AWG-250 kcmil
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Conductor - Copper Tube Std Run Range	1/2 IPS
Conductor - Copper Tube Std Run	1/2 IPS

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Dimension - Height mm	50.8 mm
Dimension - Height inch	2.00 in
Dimension - Width mm	50 mm
Dimension - Width inch	1.96 in
Dimension - L Length Overall mm	129 mm
Dimension - B Length inch	2.00 in
Dimension - Width fraction	1-24/25 in
Dimension - Length BB inch	2.38 in
Dimension - Length Overall inch	5.08 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Plated	N
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
UPC	781810077498
Type	Tube to Cable Couplers
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810077498
UPC 14 Digit GTIN	00781810077498

Logistics

Minimum Pack Quantity	15
Pallet Quantity	728

Carton Quantity1

Product Assets

[Catalog \[English\]](#)

