



# Q14F18X02B, Uninsulated Female Quick Disconnect For 16 - 14 AWG (.19 x .02)



By Burndy  
Catalog # [Q14F18X02B](#)

Uninsulated Female Quick Disconnect For 16 - 14 AWG (.19 x .02).

**Features**

- Butted Seam
- Chamfered barrel opening for quick and easy wire insertion
- Dimpled female socket detent ensure firm grip

**General**

|                        |                         |
|------------------------|-------------------------|
| Catalog Number         | Q14F18X02B              |
| Connector Type         | Female Quick Disconnect |
| Feature - Barrel Style | Chamfered               |
| Material               | Brass                   |
| Plated                 | Y                       |
| Plating Type           | Tin                     |
| Trade Name             | FINGRIP™                |
| Type                   | Disconnect Connectors   |
| UPC                    | 781810327494            |
| UPC 14 Digit GTIN      | 00781810327494          |

**Dimensions**

|                                 |          |
|---------------------------------|----------|
| Dimension - Length Overall inch | 0.66 in  |
| Dimension - Strip Length inch   | 3/8 in   |
| Dimension - Width inch          | 0.187 in |
| Dimension - Width mm            | 5 mm     |

**Conductor Related**

|                                   |                                                                                           |
|-----------------------------------|-------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size       | 16 AWG;14 AWG                                                                             |
| Conductor - Copper Str Size Range | 16 AWG - 14 AWG                                                                           |
| Conductor Size                    | 16 - 14 AWG                                                                               |
| Conductor Type                    | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |

**Certifications And Compliance**

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Certification - cULus         | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| UL Listed                     | No |

**Logistics**

|                       |       |
|-----------------------|-------|
| Carton Quantity       | 1000  |
| Minimum Pack Quantity | 1000  |
| Pallet Quantity       | 99999 |

**Product Assets**

[Catalogs - BURNDY Master Catalog - Section B - Small Terminals](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50094205](#)  
[Specifications - Q14F18X02B](#)



A Hubbell brand