



QA4C2B, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA4C2B](#)

8-4 AWG Str, 2-Hole, 1/4" Stud, .625" Spacing, Single Clamping Element, Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Copper Cable

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	8-4 AWG
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Navy Size	• 23 (7) Navy • 30 (19) Navy • 40 (19) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	8 AWG-4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Dimensions

Dimension - Pad Width inch	0.62 in
Package Height	0.000 in
Dimension - Height mm	19.1 mm
Dimension - Hole Size fraction	9/32
Dimension - Height inch	0.75 in
Dimension - Height fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.63 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Weight	0.1 lb.
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Stud Size inch	1/4
Dimension - Bolt Size fraction	1/4
Dimension - Width mm	16 mm
Dimension - D inch	1.19 in
Dimension - N inch	0.31 in
Dimension - Length Overall inch	2.00 in

Force Related

Installation Torque Recommended in-lb	110 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	QIKLUG
Product Type	Terminal
UPC	781810313084
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810313084

Logistics

Minimum Pack Quantity	1
Pallet Quantity	17150
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand