



QDA4C, 1-Hole, Heavy Duty Round Tongue Copper

By Burndy

Catalog # [QDA4C](#)

#8-4 AWG Str, 1-Hole, 3/8" Stud, Rounded Tongue, Heavy Duty Copper
Lug



Features

- Compact, high copper alloy terminal
- Joins a wide range of cable to equipment studs
- Provides low contact resistance when gripped between two contact nuts
- One-wrench installation

Application

For Joining A Wide Range Of Copper Cable To Equipment Studs

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor Size	8-4 AWG
Conductor - Copper Str Navy Size Range	23 (7) Navy-40 (19) Navy
Conductor - Copper Str Navy Size	• 23 (7) Navy • 30 (19) Navy • 40 (19) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	8 AWG-4 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Single Clamp

Dimensions

Dimension - Pad Width inch	1.00 in
Package Height	0.000 in
Dimension - Height mm	18.3 mm
Dimension - Hole Size fraction	7/16
Dimension - Height inch	0.72 in
Dimension - Height fraction	3/4
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Hole Size mm	11 mm
Dimension - Hole Size inch	0.44 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - Width mm	25 mm
Dimension - Width inch	1.00 in
Dimension - Cross Flats inch	0.56 in
Dimension - Length Overall inch	1.88 in

Force Related

Installation Torque Recommended	110 LBS/in in-lb
---------------------------------	------------------

General

Product Family	MECHANICAL
Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	QIKLUG
Product Type	Terminal
UPC	781810325001
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810325001

Logistics

Minimum Pack Quantity	1
Pallet Quantity	15400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)

