



QPX3434, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy

Catalog # [QPX3434](#)

Run and Tap 250-500 kcmil, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Nominal Diameter	0.114, 0.128, 0.144, 0.162, 0.571, 0.600, 0.630, 0.681, 0.728, 0.772, 0.813
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	• 250 kcmil • 300 kcmil • 350 kcmil



- 400 kcmil
- 450 kcmil
- 500 kcmil

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Height inch	3
Dimension - Height fraction	3
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	52 mm
Dimension - Width fraction	2-3/16 in
Dimension - Width mm	56 mm
Dimension - Width inch	2.19
Dimension - Length Overall inch	2.06 in

Force Related

Installation Torque Recommended in-lb	240 LBS/in
---------------------------------------	------------

General

Trade Name	VERSITAP™
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Sub Brand	VERSITAP
UPC	781810344002
Type	QPX
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810344002
UPC 14 Digit GTIN	00781810344002

Logistics

Pallet Quantity	1008
Carton Quantity	6



A Hubbell brand