



QA28B, 1-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA28B](#)

3/0-4/0 AWG Str., 1-Hole, 3/8" Stud, Single Clamping Element, Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Joining A Wide Range Of Cable To Equipment Pads Or Bar

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 3/0 AWG • 4/0 AWG
Conductor Size	3/0-4/0 AWG
Conductor - Copper Str Navy Size Range	150 (61) Navy-200 (61) Navy
Conductor - Copper Str Navy Size	• 150 (61) Navy • 200 (61) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.00 in
Package Height	0.000 in
Dimension - Height mm	33.3 mm
Dimension - Hole Size fraction	13/32
Dimension - Height inch	1.31 in
Dimension - Height fraction	1-5/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	57 mm
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Stud Size inch	3/8
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.06 in
Dimension - N inch	0.53 in
Dimension - Length Overall inch	2.25 in

Force Related

Installation Torque Recommended in-lb	250 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	QIKLUG
Product Type	Terminal
UPC	781810314760
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810314760
UPC 14 Digit GTIN	00781810314760

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand