



QA344N, 4-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA344N](#)



400-500 kcmil, 4-Hole, 1/2" Stud, 1.75" Spacing, Single Clamping Element, Compact Design

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	400-500 kcmil
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	400 kcmil-500 kcmil
Conductor - Copper Str Size	• 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	4
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	3.00 in
Dimension - Height mm	49.3 mm
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	1.94 in
Dimension - Height fraction	1-47/50 in
Dimension - B Length fraction	1-19/50 in
Dimension - Width inch	1.44 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - L Length Overall mm	119 mm
Dimension - B Length inch	1.38 in
Dimension - Cross Flats inch	0.81 in
Dimension - D inch	3.09 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.69 in

General

Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Trade Name	QIKLUG™
UPC	781810316702
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810316702
UPC 14 Digit GTIN	00781810316702

Logistics

Minimum Pack Quantity	6
Pallet Quantity	1044
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand