



QA34B, 1-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA34B](#)

400-500 kcmil, 1-Hole, 1/2" Stud, Single Clamping Element,
Compact Design



Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Application

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bars

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 400 kcmil • 450 kcmil • 500 kcmil
Conductor Size	400-500 kcmil
Conductor - Copper Str Navy Size Range	400 (127) Navy-500 (127) Navy
Conductor - Copper Str Navy Size	• 400 (127) Navy • 500 (127) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	400 kcmil-500 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Connector Type	Single Clamp

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Height mm	49.3 mm
Dimension - Hole Size fraction	17/32
Dimension - Height inch	1.94 in
Dimension - Height fraction	2
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	81 mm
Dimension - Hole Size mm	13 mm
Dimension - Hole Size inch	0.53 in
Dimension - Stud Size inch	1/2
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.62 in
Dimension - N inch	0.81 in
Dimension - Length Overall inch	3.19 in

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type Plated	Hexagonal Bolt N
Sub Brand	QIKLUG
UPC	781810316122
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810316122
UPC 14 Digit GTIN	00781810316122

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2160
Carton Quantity	6



A Hubbell brand