



QA462N, 2-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QA462N](#)



1100-1500 kcmil, 2-Hole, 1/2" Stud, 1.75" Spacing, Single Clamping Element, Compact Design

Features

- QIKLUG™ Terminals feature compact size, high copper alloy terminal for joining cables to equipment pads or bars
- Each element accommodates a wide range of cable
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1250 kcmil • 1300 kcmil • 1500 kcmil
Conductor Size	1100-1500 KCMIL
Conductor - Copper Str Navy Size Range	1300 (127) Navy
Conductor - Copper Str Navy Size	1300 (127) Navy
Conductor Type	• CU C Str-Size • CU C Str Navy-Size
Conductor - Copper Str Size Range	1100 kcmil-1500 kcmil

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	2
Connector Type	Single Clamp

Dimensions

Dimension - Pad Width inch	2.12 in
Package Height	0.000 in

Dimension - Height mm	73.2 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	2.88 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	133 mm
Weight	3.1 lb.
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Stud Size inch	1/2
Dimension - Bolt Size fraction	1/2
Dimension - Width mm	54 mm
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	5.25 in

Force Related

Installation Torque	600 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810318126
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810318126

Logistics

Minimum Pack Quantity	1
Pallet Quantity	216
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)



A Hubbell brand