



QB1C, 1-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QB1C](#)

#4-#1 AWG Str, Cu, Right Angled (Side Entry) Connector, 1-Hole,
1/4" Stud



Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

Application

For Joining A Range Of Copper Cable At Right Angles To
Terminal Blocks

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 4 AWG • 3 AWG • 2 AWG • 1 AWG
Conductor Size	4-1 AWG
Number Of Conductors	1
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	4 AWG-1 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Clamping Elements	1
Connector Type	Right Angle

Dimensions

Dimension - Pad Width fraction	11/16 in
Dimension - Pad Width inch	0.63 in
Package Height	0.000 in
Dimension - Height mm	25.4 mm
Dimension - Hole Size fraction	9/32
Dimension - Height inch	1.00 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Weight	0.13 lb.
Dimension - Hole Size mm	7 mm
Dimension - Hole Size inch	0.28 in
Dimension - Stud Size fraction	1/4
Dimension - Bolt Size fraction	1/4
Dimension - B Length fraction	7/8 in
Dimension - Width mm	16 mm
Dimension - Width inch	0.625 in
Dimension - B Length inch	0.88 in
Dimension - D inch	0.81 in
Dimension - N inch	0.34 in
Dimension - Length Overall inch	1.50 in

Force Related

Installation Torque	150 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Sub Brand	QIKLUG
UPC	781810324042
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810324042

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12000
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand