



QB26, 1-Hole, Heavy Duty Copper Terminal

By Burndy

Catalog # [QB26](#)

1/0-2/0 AWG Str, Right Angled (Side Entry) Connector, 1-Hole, 3/8" Stud



Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

Application

For Joining A Range Of Copper Cable At Right Angles To Terminal Blocks

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 1/0 • 2/0 AWG
Conductor Size	1/0-20 AWG
Number Of Conductors	1
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	1/0 -2/0 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Clamping Elements	1
Connector Type	Right Angle

Dimensions

Dimension - Pad Width fraction	13/16 in
Dimension - Pad Width inch	0.81 in
Package Height	0.000 in
Dimension - Height mm	28.7 mm
Dimension - Hole Size fraction	13/32

Dimension - Height inch	1.13 in
Dimension - Height fraction	1-1/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	46 mm
Weight	0.23 lb.
Dimension - Hole Size mm	10 mm
Dimension - Hole Size inch	0.41 in
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Size fraction	3/8
Dimension - B Length fraction	47/50 in
Dimension - Width mm	21 mm
Dimension - Width inch	0.81 in
Dimension - B Length inch	0.94 in
Dimension - D inch	1.00 in
Dimension - N inch	0.44 in
Dimension - Length Overall inch	1.81 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Product Family	MECHANICAL
Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	QIKLUG
Product Type	Terminal
UPC	781810324288
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810324288

Logistics

Minimum Pack Quantity	1
Pallet Quantity	8232
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)



A Hubbell brand