

QB8C, 1-Hole, Heavy Duty Copper Terminal

By Burndy
Catalog # [QB8C](#)

#14 AWG Sol-#8 AWG Str, 1-Hole, #10 Stud, Right Angled (Side Entry) Connector



Features

- Side Entry terminal
- Joins a range of cable at right angles to terminal blocks
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 14 AWG • 12 AWG • 10 AWG • 9 AWG • 8 AWG
Conductor Size	14-8 AWG
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG • 11 AWG • 10 AWG • 9 AWG • 8 AWG
Number Of Conductors	1
Conductor - Copper Solid Size Range	14 AWG-8 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	14 AWG-8 AWG

Configuration

Physical Attribute - Number of Screws	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Clamping Elements	1

Connector Type Right Angle

Dimensions

Dimension - Pad Width fraction	9/16 in
Dimension - Pad Width inch	0.56 in
Package Height	0.000 in
Dimension - Height mm	22.4 mm
Dimension - Hole Size fraction	7/32
Dimension - Height inch	0.88 in
Dimension - Height fraction	7/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	29 mm
Dimension - Hole Size mm	6 mm
Dimension - Hole Size inch	0.22 in
Dimension - Stud Size inch	#10
Dimension - Stud Size fraction	#10
Dimension - Bolt Size fraction	#10
Dimension - B Length fraction	3/4 in
Dimension - Width mm	14 mm
Dimension - Width inch	0.56 in
Dimension - B Length inch	0.75 in
Dimension - D inch	0.56 in
Dimension - N inch	0.28 in
Dimension - Length Overall inch	1.13 in

Force Related

Installation Torque	75 LBS/in
Recommended in-lb	

General

Trade Name	QIKLUG™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810324257
Type	Bolted Lugs & Terminals
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810324257

Logistics

Minimum Pack Quantity	33
-----------------------	----

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand