



QPX282C, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy
Catalog # [QPX282C](#)

Run 1/0-4/0 AWG, Tap 6-2 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections, Copper

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	EX
Status	
Certification - UL Listed Direct	No
Burial	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	1 AWG-4/0 AWG
Conductor - Copper Str Run	• 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Configuration

Physical Attribute - Number of Screws	2
Connector Type	Universal Clamp



Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	52.3 mm
Dimension - Height inch	2.06
Dimension - Height fraction	2-1/16
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	33 mm
Dimension - Width fraction	1-9/16 in
Dimension - Width mm	40 mm
Dimension - Width inch	1.56
Dimension - Length Overall inch	1.31 in

Force Related

Installation Torque Recommended	180 LBS/in in-lb
---------------------------------	------------------

General

Product Family	MECHANICAL
Trade Name	VERSITAP™
Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	No
Sub Brand	VERSITAP
Product Type	Run/Tap
UPC	781810342008
Type	QPX
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810342008
UPC 14 Digit GTIN	00781810342008

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand