



QPX3428Y, Mech. Parallel Clamp, Cu/Al, Mult. Configurations

By Burndy
Catalog # QPX3428Y



Run 250-500 kcmil, Tap 1/0-4/0 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations, Tin Plated

Features

- VERSITAP™ Type QPX-Y Parallel Clamps for copper or aluminum are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	250 kcmil-500 kcmil
Conductor - AL Str Run	• 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil
Conductor - AL Str Tap Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
Conductor - Copper Str Tap Range	1/0 -4/0 AWG
Conductor - Copper Str Tap	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.5
Dimension - Height fraction	2-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	51 mm
Dimension - Width fraction	2-1/2 in
Dimension - Width mm	62 mm
Dimension - Width inch	2.44
Dimension - Length Overall inch	2.00 in

Force Related

Installation Torque	375 LBS/in
Recommended in-lb	

General

Trade Name	VERSITAP™
Material - Hardware Plated	DURIUM™ Silicon Bronze Y
UPC	781810343012
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810343012
UPC 14 Digit GTIN	00781810343012

Logistics

Minimum Pack Quantity	1	Temperature Rating	194
Pallet Quantity	1		
Carton Quantity	1		

Operational

Product Assets

[Catalog \[English\]](#)



A Hubbell brand