



QPX342C, Mech. Parallel Clamp for Cu, Mult. Configurations

By Burndy
Catalog # QPX342C

Run 250-500 kcmil, Tap #6-#2 AWG, Capable of Tee, Cross, Parallel, Butt and Tap Configurations

Features

- VERSITAP™ Type QPX Parallel Clamps for copper are capable of Tee, Cross, Parallel, Butt and Tap configurations
- Range-taking, only 10 connectors are required to accommodate conductor sizes from #6 Stranded to 1000 kcmil
- Edges are rounded for easy taping

Application

For Tee, Cross, Parallel, Butt And Tap Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL486A-486B
Standards - RoHS Compliance Status	EX
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor Type	• CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG-2 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG



- 2 AWG

Configuration

Connector Type	Universal Clamp
----------------	-----------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	63.5 mm
Dimension - Height inch	2.38
Dimension - Height fraction	2-3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	35 mm
Dimension - Width fraction	1-7/8 in
Dimension - Width mm	48 mm
Dimension - Width inch	1.88
Dimension - Length Overall inch	1.38 in

Force Related

Installation Torque Recommended in-lb	180 LBS/in
---------------------------------------	------------

General

Trade Name	VERSITAP™
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Sub Brand	VERSITAP
UPC	781810343005
Type	QPX
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810343005
UPC 14 Digit GTIN	00781810343005

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1200
Carton Quantity	2



A Hubbell brand