


QR28, Mech. Heavy Duty Copper Splice Reducer

By Burndy
Catalog # [QR28](#)

Mechanical Splice / Reducer, 3/0-4/0 Str Cu, Compact Style, 1-Wrench Installation



Features

- Type QR QIKLINK™ splice or reducer features a neat, compact, easy to tape installation
- One-wrench installation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	3/0 AWG 4/0 AWG
Conductor Size	3/0-4/0 AWG
Conductor - Copper Str Size B	3/0 AWG 4/0 AWG
Conductor - Copper Str Size A Range	3/0 AWG-4/0 AWG
Conductor - Copper Solid Size A	3/0 AWG 4/0 AWG
Conductor - Copper Solid Size B	3/0 AWG 4/0 AWG
Conductor - Copper Solid Size A Range	3/0 AWG-4/0 AWG
Conductor - Copper Solid Size B Range	3/0 AWG-4/0 AWG
Conductor Type	- CU C Str-Size A - CU C Str-Size B - CU C Solid-Size A - CU C Solid-Size B
Conductor - Copper Str Size B Range	3/0 AWG-4/0 AWG

Configuration

Physical Attribute - Number of Screws	2
Connector Type	In-Line

Dimensions

Package Height	0.000 in
Dimension - Height mm	28.7 mm
Dimension - Height inch	1.13 in
Dimension - Height fraction	1-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	60 mm
Dimension - Width fraction	1 in
Dimension - B Length fraction	1-1/16 in
Dimension - Width mm	25 mm
Dimension - Width inch	1.00 in
Dimension - B Length inch	1.06 in
Dimension - Length Overall inch	2.38 in

Force Related

Installation Torque Recommended in-lb	250 LBS/in
---------------------------------------	------------

General

Trade Name	QIKLINK™
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
UPC	781810334515
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810334515

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)



A Hubbell brand