



TP1638, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # [TP1638](#)

Vinyl Ring Terminal For 22 - 16 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG
Conductor - Copper Solid Size	• 20 • 18 AWG • 17 AWG • 16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor Size	22 - 16 AWG
Conductor - Copper Str Size Range	20 AWG - 16 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall mm	29 mm
Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Dimension - Strip Length inch	13/64
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.45 in
Dimension - Bolt Size fraction	3/8
Cable Insulation Diameter Maximum	0.145 in
Dimension - Length Overall inch	1.15 in
Dimension - Diameter Max Size inch	0.15 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	COMPRESSION TERMINAL, VINYLUG
Color Code	Red
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	Ring Tongue
UPC 12 Digit	781810715444
UPC 14 Digit GTIN	00781810715444
Material	Copper
Plating Type	Tin
UPC	781810715444

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200

Pallet Quantity 99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand