




UH153W, Substation Copper Bus Support, 1" IPS, 3" Bolt Dia, 3/8" Bolt

By Burndy
Catalog # [UH153W](#)

Cast Cu Alloy Bus Support-Complete Part, 1" IPS, 3" Bolt Dia, 3/8" Bolt



Features

- Type UH Copper Bus Supports for Supporting Copper Tube to Base
- High copper alloy bus support for mounting tube on a post or pedestal type insulator
- Single bolt allows rotation to any angle
- Rotate cap 180 degrees for slip or rigid fit
- Supplied with hardware for mounting to cap of insulator
- Suffix -B on the catalog number denotes base mounting hardware is supplied

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	EX
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Number Of Conductors	1
Conductor - Connection Combination	Base to Tube
Conductor Type	• CU Tube Std-Size • CU Tube EH-Size
Conductor - Copper Tube Std Size Range	1 IPS
Conductor - Copper Tube Std Size	1 IPS
Conductor - Copper Tube EH Size Range	1 IPS
Conductor - Copper Tube EH Size	1 IPS

Configuration

Connector Type	Bus Support
----------------	-------------

Dimensions

Bolt Circle Diameter	3.00 in
Dimension - G inch	2.00 in
Package Height	0.000 in
Dimension - Height mm	76.2 mm
Dimension - Hole Size fraction	9/16
Dimension - Height inch	3.00 in
Package Weight	0.000 lb.
Dimension - Width mm	73 mm
Dimension - Width inch	2.88 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	2.50 in
Dimension - Hole Size inch	0.56 in

Force Related

Installation Torque	240 in-lb
Recommended in-lb	

General

Plated	Y
Material - Hardware	DURIUM™ Silicon Bronze
Fitting Type	Slip or Rigid
One Wrench Installation	Y
UPC	781810119754
Type	Cable or Tube to Insulator Bus Supports
Mounting Hardware	1/2-13 x 1" LG
Material	Copper Alloy
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810119754
Hardware Type	Cap mounting kit (w/o nuts)
UPC 14 Digit GTIN	00781810119754

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)