



BURNDY

**UHR133, Substation Copper Bus Support, 6 Str AWG-500 kcmil, Copper
Pipe: 1/8"-1/2" IPS, 3" Bolt Dia**

By Burndy

Catalog # [UHR133](#)

Cast Cu Alloy Bus Support, CU Str. Size: 6 AWG - 500 Kcmil, CU Pipe Size: 1/8"-1/2" IPS, 3 IN Bolt Circle Dia



Features

- Type UHR Copper Bus Supports for Supporting Copper Cable or Tube to Base
- Suitable for mounting a wide range of cable or tube on post or pedestal type insulators
- Single bolt allows rotation to any angle
- Supplied with hardware for mounting to cap of insulator
- Suffix -B at the end of catalog denotes base mounting hardware is included

Application

Substation

Specifications

Certification - UL Recognized
No
Certification - cULus
No
Certification - ETL
No
Standards - RoHS Compliance Status
EX
UL Listed
No
Certification - CSA Approved
No

Conductor

Conductor - Copper Str Size

- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil
- 300 kcmil
- 350 kcmil
- 400 kcmil
- 450 kcmil
- 500 kcmil

Number Of Conductors
1
Conductor - Connection Combination
Base to Tube or Cable
Conductor - Copper Str Size Range
6 AWG-500 kcmil
Conductor - Copper Tube Std Size Range
1/8 IPS-1/2 IPS
Conductor - Copper Tube Std Size

- 1/8 IPS
- 1/4 IPS
- 3/8 IPS
- 1/2 IPS

Configuration

Connector Type
Bus Support

Dimensions

Dimension - G inch
1.75 in
Package Height
0.000 in
Dimension - Height mm
76 mm
Dimension - Hole Size fraction
9/16
Dimension - Height inch
3.00 in
Dimension - Height fraction
3 in
Package Weight
0.000 lb.
Package Length
0.000 in
Package Width
0.000 in
Dimension - Width fraction
2-1/4 in
Dimension - Hole Size inch

0.56 in
Bolt Circle Diameter
3.00 in
Dimension - B Length fraction
3-5/8 in
Dimension - Width mm
57 mm
Dimension - Width inch
2.25 in
Dimension - B Length inch
3.56 in

Force Related

Installation Torque Recommended in-lb
240 in-lb

General

Material - Hardware
DURIUM™ Silicon Bronze
One Wrench Installation
Y
Plated
N
Fitting Type
Rigid Conduit
UPC
781810004579
Type
Cable or Tube to Insulator Bus Supports
Mounting Hardware
1/2 X 1" Hot Dipped Galv. Steel Hex. Head Bolts
Material
Copper Alloy
Plating Type
Unplated
UPC 12 Digit
781810004579
Hardware Type
Cap mounting kit (w/o nuts)
UPC 14 Digit GTIN
00781810004579

Logistics

Minimum Pack Quantity
1
Pallet Quantity
1
Carton Quantity
1

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-UHR133-SPEC-EN | REV 5/2026