



UHR135, Substation Copper Bus Support, 6 AWG Str-500 kcmil, Cu Pipe Size: 1/8"-1/2" IPS, 5" Bolt Circle Dia

By Burndy
Catalog # [UHR135](#)

Cast Cu Alloy Bus Support, CU Str. Size: 6 AWG - 500 Kcmil, CU Pipe Size: 1/8"-1/2" IPS, 5 IN Bolt Circle Dia

Features

- Type UHR Copper Bus Supports for Supporting Copper Cable or Tube to Base
- Suitable for mounting a wide range of cable or tube on post or pedestal type insulators
- Single bolt allows rotation to any angle
- Supplied with hardware for mounting to cap of insulator
- Suffix -B at the end of catalog denotes base mounting hardware is included

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Number Of Conductors	1
Conductor - Connection Combination	Base to Tube or Cable
Conductor - Copper Str Size Range	6 AWG-500 kcmil



Conductor - Copper Tube Std Size Range	1/8 IPS-1/2 IPS
Conductor - Copper Tube Std Size	• 1/8 IPS • 1/4 IPS • 3/8 IPS • 1/2 IPS

Configuration

Connector Type	Bus Support
----------------	-------------

Dimensions

Dimension - G inch	2.12 in
Dimension - Height mm	86 mm
Dimension - Hole Size fraction	11/16
Dimension - Height inch	3.38 in
Dimension - Height fraction	3-3/8 in
Dimension - Width fraction	2-1/4 in
Dimension - Hole Size inch	0.69 in
Bolt Circle Diameter	5.00 in
Dimension - B Length fraction	3-5/8 in
Dimension - Width mm	57 mm
Dimension - Width inch	2.25 in
Dimension - B Length inch	3.56 in

Force Related

Installation Torque Recommended in-lb	240 in-lb
---------------------------------------	-----------

General

Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Plated	N
Fitting Type	Rigid Conduit
UPC	781810004586
Type	Cable or Tube to Insulator Bus Supports
Mounting Hardware	5/8 X 1" Hot Dipped Galv. Steel Hex. Head Bolts
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810004586
Hardware Type	Cap mounting kit (w/o nuts)
UPC 14 Digit GTIN	00781810004586

Logistics

Minimum Pack Quantity	8
Pallet Quantity	100

Carton Quantity1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand