



UCU28AC, Al Mech. Parallel Riser Tap with Cover

By Burndy

Catalog # [UCU28AC](#)

#2-4/0 Str Al/Cu Run, #10 Sol-#2 Str Al/Cu Tap, Parallel Riser Tap w/Cover



Features

- Parallel-groove riser tap with insulation cover for copper and aluminum
- Wide range-taking assembly for apartment house/light industrial applications
- Cover and connector are packaged together

Application

For Apartment House And Light Industrial Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	2 AWG-4/0 AWG
Conductor - AL Str Run	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - AL Str Tap Range	8 AWG-2 AWG
Conductor - AL Str Tap	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Run Range	2 AWG-4/0 AWG
Conductor - Copper Str Run	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG

Conductor - Copper Solid Tap Range	• 4/0 AWG 10 AWG-2 AWG
Conductor - Copper Solid Tap	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor Type	• AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap
Conductor - Copper Str Tap Range	10 AWG-2 AWG
Conductor - Copper Str Tap	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG

Configuration

Connector Type	Riser Tap
----------------	-----------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	46 mm
Dimension - Height inch	1.81 in
Dimension - Height fraction	1-13/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	67 mm
Dimension - Width fraction	2-1/4 in
Dimension - Screw Size inch	5/16
Dimension - Width mm	57 mm

Dimension - Width inch	2.24 in	Plating Type	Unplated
Dimension - Length Overall inch	2.62 in	UPC 12 Digit	781810006276
		UPC 14 Digit GTIN	00781810006276
Force Related		Logistics	
Installation Torque Recommended in-lb	120 LBS/in	Minimum Pack Quantity	1
		Pallet Quantity	3000
		Carton Quantity	20
General		Operational	
Product Family	MECHANICAL	Temperature Rating	194
Plated	No		
Sub Brand	TAPIT		
Product Type	Run/Tap		
UPC	781810006276	Product Assets	
Type	UCU-AC	Catalog [English]	
Material	Aluminum		



A Hubbell brand