



Substation - Copper V Type T Connector

By Burndy
Catalog # VT2525

High Cu Alloy VARITAP T-Connector, Bolted, Cable to Cable, #6 Sol - 1/0 Str(Run), #6 Sol - 1/0 Str(Tap)

Features

- High copper alloy T-connector for cable run, cable tap
- V-Bolt clamping elements accommodate large range of cable and are particularly suited for extra flexible cable
- 1-wrench installation

Application

Substation

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	6 AWG-1/0 AWG
Conductor - Copper Str Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - Copper Solid Run Range	6 AWG-1/0 AWG
Conductor - Copper Solid Run	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG
Conductor - Connection Combination	Cable to Cable
Conductor - Copper Solid Tap Range	6 AWG-1/0 AWG
Conductor - Copper Solid Tap	• 6 AWG

Conductor Type	• 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG • CU C Str-Run • CU C Str-Tap
Conductor - Copper Str Tap Range	6 AWG-1/0 AWG
Conductor - Copper Str Tap	• 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 AWG

Configuration

Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Number of Run Conductors	1
Connector Type	T-Connector

Dimensions

Package Height	0.000 in
Dimension - Height mm	9.7 mm
Dimension - Height inch	0.38 in
Dimension - Height fraction	1-5/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	35 mm
Dimension - Width fraction	1-7/16 in
Dimension - Width mm	14 mm
Dimension - Width inch	0.56 in
Dimension - Length Overall inch	1.37 in

Force Related

Installation Torque Recommended in-lb	0.79 LBS/in
Installation Torque Recommended Tap in-lb	385 LBS/in

Installation Torque	385 LBS/in	Plating Type	Unplated
Recommended Run in-lb		UPC 12 Digit	781810005552
		UPC 14 Digit GTIN	00781810005552
General		Logistics	
Trade Name	VARITAP™	Minimum Pack Quantity	20
Material - Hardware	DURIUM™ Silicon Bronze	Pallet Quantity	432
One Wrench Installation	Y	Carton Quantity	12
Plated	N		
UPC	781810005552		
Type	Bolted Tees		
Material	Copper Alloy		
		Product Assets	
		Catalog [English]	



A Hubbell brand