



WAD1015, WEJTAP Applied In-Line Disconnect Switch

By Burndy
Catalog # [WAD1015](#)



MAX RANGE: .398 - .502 ACSR: 1/0 (6/1), 2/0 (6/1), 3/0 (6/1)
AAC: 1/0, 2/0, 3/0 15 kV, 110 BIL.

Features

- WEJTAP In-Line Disconnect utilizes proven WEJTAP technology in combination with industry standard components to provide reliable performance of switch applications
- Designed for use in gloving and hot stick applications in conjunction with an industry standard load break tool
- Dual insulators minimize the switch movement during opening and closing of the blade
- In-Line Disconnect is removable and reusable

General

Catalog Number	WAD1015
Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810560488
UPC 14 Digit GTIN	00781810560488

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	30.58 (7) kcmil
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil

Conductor - ACSR Str Size	1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	1 (6/1) Robin AWG-3/0 (6/1) Pigeon AWG
Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Size Range	1/0 AWG-3/0 AWG
Conductor Type	• AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	UI
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section J - OH Distribution / Transmission](#)
[Customer Notices - Prop 65 Notice](#)
[Excel Files - Burndy-CPI WEJTAP Connector Selector](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10083326](#)
[Sell Sheets - In-Line Switch Overview](#)
[Specifications - WAD1015](#)



A Hubbell brand