



WCY145, WEJTAP Connector

By Burndy
Catalog # [WCY145](#)



Aluminum Overhead Wedge Tap Connector, 1.533 Dia. To 1.032 Dia. (Run), 1.094 Dia. To 1.032 Dia. (Tap)

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	800 kcmil-1800 kcmil
Conductor - AL Str Run	• 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil • 1033 kcmil • 1100 kcmil • 1113 kcmil • 1192 kcmil • 1200 kcmil • 1250 kcmil • 1272 kcmil • 1300 kcmil • 1351 kcmil • 1400 kcmil • 1431 kcmil • 1500 kcmil • 1590 kcmil • 1600 kcmil • 1700 kcmil • 1750 kcmil • 1800 kcmil
Conductor - AL Str Tap Range	800 kcmil-900 kcmil
Conductor - AL Str Tap	• 800 kcmil • 874 kcmil • 900 kcmil
Conductor - ACSR Str Run Range	666.6 (24/7) Flamingo kcmil-1590 (54/19) Falcon kcmil
Conductor - ACSR Str Run	• 666.6 (24/7) Flamingo kcmil • 715.5 (54/7) Crow kcmil

- 715.5 (24/7) Stilt kcmil
- 715.5 (26/7) Starling kcmil
- 715.5 (30/19) Redwing kcmil
- 795 (54/7) Condor kcmil
- 795 (26/7) Drake kcmil
- 795 (30/19) Mallard kcmil
- 874.5 (54/7) Crane kcmil
- 900 (54/7) Canary kcmil
- 954 (45/7) Rail kcmil
- 954 (54/7) Cardinal kcmil
- 1033.5 (45/7) Ortolan kcmil
- 1033.5 (54/7) Curlew kcmil
- 1113 (54/19) Finch kcmil
- 1192.5 (45/7) Bunting kcmil
- 1192.5 (54/19) Grackle kcmil
- 1272 (54/19) Pheasant kcmil
- 1351.5 (54/19) Martin kcmil
- 1431 (54/19) Plover kcmil
- 1510.5 (45/7) Nuthatch kcmil
- 1590 (45/7) Lapwing kcmil
- 1590 (54/19) Falcon kcmil
- 666.6 (24/7) Flamingo kcmil-795 (26/7) Drake kcmil
 - 666.6 (24/7) Flamingo kcmil
 - 715.5 (54/7) Crow kcmil
 - 715.5 (24/7) Stilt kcmil
 - 715.5 (26/7) Starling kcmil
 - 715.5 (30/19) Redwing kcmil
 - 795 (54/7) Condor kcmil
 - 795 (26/7) Drake kcmil

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

Configuration

Connector Type	Tap
----------------	-----

Dimensions


Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.75 in
Package Width	0.000 in

General

UPC	781810231944
Material	Aluminum
UPC 12 Digit	781810231944

Logistics

Pallet Quantity1



Product Assets

[Catalog \[English\]](#)