



WCY51PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY51PB](#)

Wejtap connector installed with Yellow booster, .537-.750 Run,
.324-.557 (Tap)



Features

- WEJTAP Connector, packaged with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance	NC
Status	
Buy American Compliant	No
EU RoHS Indicator	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/O AWG-450 kcmil
Conductor - AL Str Run	

- 4/O AWG
- 250 kcmil
- 266 kcmil
- 300 kcmil
- 336 kcmil
- 350 kcmil
- 397 kcmil
- 400 kcmil
- 450 kcmil

Conductor - AL Str Tap Range	1 AWG-250 kcmil
Conductor - AL Str Tap	

- 1 AWG
- 1/O AWG
- 2/O AWG
- 3/O AWG
- 4/O AWG
- 250 kcmil

Conductor Type	
	• ACSR C Str-Run
	• AL C Str-Run
	• ACSR C Str-Tap
	• AL C Str-Tap

Conductor - ACSR Str Run Range	4/O (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run	

- 4/O (6/1) Penguin AWG
- 80 (8/1) Grouse kcmil
- 101.8 (12/7) Petrel kcmil
- 110.8 (12/7) Minorca kcmil
- 134.6 (12/7) Leghorn kcmil
- 159 (12/7) Guinea kcmil
- 176.9 (12/7) Dotterel kcmil

- 190.8 (12/7) Dorking kcmil
- 211.3 (12/7) Cochin kcmil
- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil
- 397.5 (24/7) Brant kcmil
- 397.5 (26/7) Ibis kcmil

Conductor - ACSR Str Tap Range	2 (7/1) Sparate AWG-4/O (6/1) Penguin AWG
Conductor - ACSR Str Tap	
	• 2 (7/1) Sparate AWG
	• 1 (6/1) Robin AWG
	• 1/O (6/1) Raven AWG
	• 2/O (6/1) Quail AWG
	• 3/O (6/1) Pigeon AWG
	• 4/O (6/1) Penguin AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Dimension - F Width Center to Center inch	3 in

General

Color	Yellow
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810870457
Type	Wejtap Connector with Booster
Material	Aluminum
UPC 12 Digit	781810870457
UPC 14 Digit GTIN	00781810870457

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

[Catalog \[English\]](#)

