



WCY56, WEJTAP Connector

By Burndy
Catalog # WCY56



WEJTAP Assembly, 0.75-0.54(Run), 0.75-0.52(Tap)

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/O AWG-450 kcmil
Conductor - AL Str Run	• 4/O AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
Conductor - AL Str Tap Range	4/O AWG-450 kcmil
Conductor - AL Str Tap	• 4/O AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Conductor - ACSR Str Run Range	4/O (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run	• 4/O (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil • 397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Tap Range	4/O (6/1) Penguin AWG-397.5 (24/7) Brant kcmil
Conductor - ACSR Str Tap	• 4/O (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil • 266.8 (26/7) Partridge kcmil • 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil • 397.5 (18/1) Chickadee kcmil • 397.5 (24/7) Brant kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP

UPC	781810874202
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810874202
UPC 14 Digit GTIN	00781810874202

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand