

WCY62, WEJTAP Connector

By Burndy
Catalog # [WCY62](#)



Wejtap Assembly, Installed With Yellow Booster, Sum of diameters: 1.594 (Max), 1.379 (Min)

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	• 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil
Conductor - AL Str Tap Range	4/O AWG-450 kcmil
Conductor - AL Str Tap	• 4/O AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap

Conductor - ACSR Str Run Range
Conductor - ACSR Str Run

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

- AL C Str-Tap
- 336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil
- 397.5 (24/7) Brant kcmil
- 397.5 (26/7) Ibis kcmil
- 397.5 (30/7) Larkspur kcmil
- 477.0 (18/1) Pelican kcmil
- 477.0 (24/7) Flicker kcmil
- 477.0 (26/7) Hawk kcmil
- 477. (30/7) Hen kcmil
- 500.0 (30/7) Heron kcmil
- 556.5 (24/7) Parakeet kcmil
- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil
- 4/O (6/1) Penguin AWG-397.5 (24/7) Brant kcmil
- 4/O (6/1) Penguin AWG
- 80 (8/1) Grouse kcmil
- 101.8 (12/7) Petrel kcmil
- 110.8 (12/7) Minorca kcmil
- 134.6 (12/7) Leghorn kcmil
- 159 (12/7) Guinea kcmil
- 176.9 (12/7) Dotterel kcmil
- 190.8 (12/7) Dorking kcmil
- 211.3 (12/7) Cochin kcmil
- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil
- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil
- 397.5 (24/7) Brant kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Package Height	0.000 in

Package Weight	0.000 lb.	Material	Aluminum
Package Length	0.000 in	UPC 12 Digit	781810874509
Dimension - F Width Center to Center inch	3 in	UPC 14 Digit GTIN	00781810874509
Package Width	0.000 in		
General		Logistics	
Trade Name	WEJTAP™	Minimum Pack Quantity	10
Sub Brand	WEJTAP	Pallet Quantity	700
UPC	781810874509	Carton Quantity	10
Type	Wejtap Connector	Product Assets	
		Catalog [English]	



A Hubbell brand