



WCY75PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY75PB](#)



Wejtap connector installed with Yellow booster, .889-1.133 Run, .763-.927 (Tap)

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	400-650
Conductor - AL Str Tap	• 400 • 450 • 477 • 500 • 550 • 556.5 • 600 • 636 • 650
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen

- 556.5 (24/7) Parakeet
- 556.5 (26/7) Dove
- 556.5 (30/7) Eagle
- 605 (24/7) Peacock
- 605 (26/7) Squab
- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 397.5 (18/1) Chickadee-556.5 (26/7) Dove
- 397.5 (18/1) Chickadee
- 397.5 (24/7) Brant
- 397.5 (26/7) Ibis
- 397.5 (30/7) Larkspur
- 477.0 (18/1) Pelican
- 477.0 (24/7) Flicker
- 477.0 (26/7) Hawk
- 477.0 (30/7) Hen
- 556.5 (24/7) Parakeet
- 556.5 (26/7) Dove

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.9 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870693
Material	Aluminum
UPC 12 Digit	781810870693
UPC 14 Digit GTIN	00781810870693

Logistics

Minimum Pack Quantity 5

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-WCY75PB-SPEC-EN | REV 5/2026