



WCY81, WEJTAP Connector

By Burndy
Catalog # [WCY81](#)



Wejtap connector installed with yellow booster, .889-1.133 (Run), .364-.608 (Tap)

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	1-300
Conductor - AL Str Tap	• 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet

Conductor - ACSR Str Tap Range	556.5 (26/7) Dove
Conductor - ACSR Str Tap	556.5 (30/7) Eagle
	605 (24/7) Peacock
	605 (26/7) Squab
	605 (30/19) Teal
	636 (24/7) Rook
	636 (26/7) Grosbeak
	636 (30/19) Egret
	666.6 (24/7) Flamingo
	715.5 (54/7) Crow
	715.5 (26/7) Starling
	715.5 (30/19) Redwing
	795 (54/7) Condor
	795 (26/7) Drake
	795 (30/19) Mallard
	1 (6/1) Robin-266.8 (18/1) Waxwing
	1 (6/1) Robin
	1/0 (6/1) Raven
	2/0 (6/1) Quail
	3/0 (6/1) Pigeon
	4/0 (6/1) Penguin
	80 (8/1) Grouse
	101.8 (12/7) Petrel
	110.8 (12/7) Minorca
	134.6 (12/7) Leghorn
	159 (12/7) Guinea
	176.9 (12/7) Dotterel
	190.8 (12/7) Dorking
	203.2 (16/9) Brahma
	211.3 (12/7) Cochin
	266.8 (18/1) Waxwing

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™	Minimum Pack Quantity	5
UPC	781810875452	Pallet Quantity	350
Material	Aluminum	Carton Quantity	5
UPC 12 Digit	781810875452		
UPC 14 Digit GTIN	00781810875452		

Product Assets

[Catalog \[English\]](#)

Logistics



A Hubbell brand