



WCY82, WEJTAP Connector

By Burndy
Catalog # [WCY82](#)



WEJTAP Connector, 1.133 - 0.889 (Run), 0.436 - 0.324 (Tap),
Installed With Yellow Booster

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	2-3/0
Conductor - AL Str Tap	• 2 • 1 • 1/0 • 2/0 • 3/0
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock

- 605 (26/7) Squab
- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 2 (6/1) Sparrow-2/0 (6/1) Quail
- 2 (6/1) Sparrow
- 2 (7/1) Sparate
- 1 (6/1) Robin
- 1/0 (6/1) Raven
- 2/0 (6/1) Quail

Conductor - ACSR Str Tap
Range
Conductor - ACSR Str Tap

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810875506
Material	Aluminum
UPC 12 Digit	781810875506
UPC 14 Digit GTIN	00781810875506

Logistics

Minimum Pack Quantity	5
Pallet Quantity	350
Carton Quantity	5



A Hubbell brand