



WCY91PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY91PB](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 1.130 - 0.856 (Tap), With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600-1000
Conductor - AL Str Run	• 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	556.5-900
Conductor - AL Str Tap	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet-1033.5 (54/7) Curlew

Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab • 605 (30/19) Teal • 636 (24/7) Rook • 636 (26/7) Grosbeak • 636 (30/19) Egret • 666.6 (24/7) Flamingo • 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane • 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew
Conductor - ACSR Str Tap Range	477.0 (26/7) Hawk-1113 (54/19) Finch
Conductor - ACSR Str Tap	• 477.0 (26/7) Hawk • 477.0 (30/7) Hen • 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab • 605 (30/19) Teal • 636 (24/7) Rook • 636 (26/7) Grosbeak • 636 (30/19) Egret • 666.6 (24/7) Flamingo • 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane • 900 (54/7) Canary • 954 (54/7) Cardinal • 1033.5 (54/7) Curlew • 1113 (54/19) Finch

Configuration

Connector Type	Tap	UPC	781810870853
Dimensions	1.97 in	Material	Aluminum
		UPC 12 Digit	781810870853
		UPC 14 Digit GTIN	00781810870853
Dimension - G inch	1.97 in		
Dimension - F Width Center to Center inch	3.5 in		
		Logistics	
		Minimum Pack Quantity	5
		Product Assets	
Color	Yellow		
Trade Name	WEJTAP™	Catalog [English]	



A Hubbell brand