



WCY94, WEJTAP Connector

By Burndy
Catalog # [WCY94](#)



Wejtap Assembly, 1.250-0.893 (Run), 0.750-0.588 (Tap), Installed
With yellow Booster

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600 kcmil-1000 kcmil
Conductor - AL Str Run	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Tap Range	300 kcmil-450 kcmil
Conductor - AL Str Tap	• 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil • 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil

- 605 (30/19) Teal kcmil
 - 636 (24/7) Rook kcmil
 - 636 (26/7) Grosbeak kcmil
 - 636 (30/19) Egret kcmil
 - 666.6 (24/7) Flamingo kcmil
 - 715.5 (54/7) Crow kcmil
 - 715.5 (24/7) Stilt kcmil
 - 715.5 (26/7) Starling kcmil
 - 715.5 (30/19) Redwing kcmil
 - 795 (54/7) Condor kcmil
 - 795 (26/7) Drake kcmil
 - 795 (30/19) Mallard kcmil
 - 874.5 (54/7) Crane kcmil
 - 900 (54/7) Canary kcmil
 - 954 (45/7) Rail kcmil
 - 954 (54/7) Cardinal kcmil
 - 1033.5 (45/7) Ortolan kcmil
 - 1033.5 (54/7) Curlew kcmil
- | | |
|--------------------------------|--|
| Conductor - ACSR Str Tap Range | 266.8 (18/1) Waxwing kcmil-397.5 (18/1) Chickadee kcmil |
| Conductor - ACSR Str Tap | <ul style="list-style-type: none">• 266.8 (18/1) Waxwing kcmil• 266.8 (26/7) Owl kcmil• 266.8 (26/7) Partridge kcmil• 300.0 (26/7) Ostrich kcmil• 336.4 (18/1) Merlin kcmil• 336.4 (26/7) Linnet kcmil• 336.4 (30/7) Oriole kcmil• 397.5 (18/1) Chickadee kcmil |

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.97 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810876107
Material	Aluminum
UPC 12 Digit	781810876107

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)

