




WCY96, WEJTAP Connector

By Burndy
Catalog # [WCY96](#)

WEJTAP Connector, 1.250 - 0.893 (Run), 0.609 - 0.364 (Tap),
Installed With Yellow Booster



Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600-1000
Conductor - AL Str Run	• 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	1/0-266.8
Conductor - AL Str Tap	• 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet-1033.5 (54/7) Curlew
Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab • 605 (30/19) Teal • 636 (24/7) Rook • 636 (26/7) Grosbeak • 636 (30/19) Egret

Conductor - ACSR Str Tap Range
Conductor - ACSR Str Tap

- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 874.5 (54/7) Crane
- 900 (54/7) Canary
- 954 (54/7) Cardinal
- 1033.5 (54/7) Curlew
- 1/0 (6/1) Raven-266.8 (18/1) Waxwing
- 1/0 (6/1) Raven
- 2/0 (6/1) Quail
- 3/0 (6/1) Pigeon
- 4/0 (6/1) Penguin
- 80 (8/1) Grouse
- 101.8 (12/7) Petrel
- 110.8 (12/7) Minorca
- 134.6 (12/7) Leghorn
- 159 (12/7) Guinea
- 176.9 (12/7) Dotterel
- 190.8 (12/7) Dorking
- 203.2 (16/9) Brahma
- 211.3 (12/7) Cochin
- 266.8 (18/1) Waxwing

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.96 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810876206
Material	Aluminum
UPC 12 Digit	781810876206
UPC 14 Digit GTIN	00781810876206

Logistics

Minimum Pack Quantity	5
Pallet Quantity	1

Carton Quantity5

Product Assets

[Catalog \[English\]](#)



A Hubbell brand