



WCY54PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY54PB](#)



Wejtap Assembly, 4/O AWG-450 kcmil (Run), 2/O AWG-300 kcmil (Tap), Wiring taps

Features

- WEJTAP Connector, packaged with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance	NC
Status	
EU RoHS Indicator	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	4/O AWG-450 kcmil
Conductor - AL Str Run	• 4/O AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil

Conductor - AL Str Tap Range	2/O AWG-300 kcmil
Conductor - AL Str Tap	• 2/O AWG • 3/O AWG • 4/O AWG • 250 kcmil • 266 kcmil • 300 kcmil

Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
----------------	---

Conductor - ACSR Str Run Range	4/O (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run	• 4/O (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil

Conductor - ACSR Str Tap Range	2/O (6/1) Quail AWG-266.8 (26/7) Owl kcmil
Conductor - ACSR Str Tap	• 2/O (6/1) Quail AWG • 3/O (6/1) Pigeon AWG • 4/O (6/1) Penguin AWG • 80 (8/1) Grouse kcmil • 101.8 (12/7) Petrel kcmil • 110.8 (12/7) Minorca kcmil • 134.6 (12/7) Leghorn kcmil • 159 (12/7) Guinea kcmil • 176.9 (12/7) Dotterel kcmil • 190.8 (12/7) Dorking kcmil • 211.3 (12/7) Cochin kcmil • 203.2 (16/9) Brahma kcmil • 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.37 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Color	Yellow
Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810870488

Type	Wejtap Connector with Booster	Product Assets
Material	Aluminum	Catalog [English]
UPC 12 Digit	781810870488	
UPC 14 Digit GTIN	00781810870488	



A Hubbell brand