



WCY64, WEJTAP Connector

By Burndy
Catalog # [WCY64](#)

Wejtap Assembly, Installed With Yellow Booster, Sum of diameters: 1.421 (Max), 1.216 (Min)



Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	350 kcmil 397 kcmil 400 kcmil 450 kcmil 477 kcmil 500 kcmil 550 kcmil 556 kcmil 600 kcmil 636 kcmil 650 kcmil 700 kcmil
Conductor - AL Str Tap Range	2/0 AWG-300 kcmil
Conductor - AL Str Tap	2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil 266 kcmil 300 kcmil
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap
Conductor - ACSR Str Run Range	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil

Conductor - ACSR Str Run

- 336.4 (18/1) Merlin kcmil
- 336.4 (26/7) Linnet kcmil
- 336.4 (30/7) Oriole kcmil
- 397.5 (18/1) Chickadee kcmil
- 397.5 (24/7) Brant kcmil
- 397.5 (26/7) Ibis kcmil
- 397.5 (30/7) Larkspur kcmil
- 477.0 (18/1) Pelican kcmil
- 477.0 (24/7) Flicker kcmil
- 477.0 (26/7) Hawk kcmil
- 477. (30/7) Hen kcmil
- 500.0 (30/7) Heron kcmil
- 556.5 (24/7) Parakeet kcmil
- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil

Conductor - ACSR Str Tap Range

1/0 (6/1) Raven AWG-300.0 (26/7) Ostrich kcmil

Conductor - ACSR Str Tap

- 1/0 (6/1) Raven AWG
- 2/0 (6/1) Quail AWG
- 3/0 (6/1) Pigeon AWG
- 4/0 (6/1) Penguin AWG
- 80 (8/1) Grouse kcmil
- 101.8 (12/7) Petrel kcmil
- 110.8 (12/7) Minorca kcmil
- 134.6 (12/7) Leghorn kcmil
- 159 (12/7) Guinea kcmil
- 176.9 (12/7) Dotterel kcmil
- 190.8 (12/7) Dorking kcmil
- 211.3 (12/7) Cochin kcmil
- 203.2 (16/9) Brahma kcmil
- 266.8 (18/1) Waxwing kcmil
- 266.8 (26/7) Owl kcmil
- 266.8 (26/7) Partridge kcmil
- 300.0 (26/7) Ostrich kcmil

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810874608
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810874608
UPC 14 Digit GTIN	00781810874608



A Hubbell brand

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)