



WCY65, WEJTAP Connector

By Burndy
Catalog # [WCY65](#)



Wejtap connector installed with yellow booster, .683-.940 (Run),
.382-.562 (Tap)

Features

- WEJTAP Connector installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Standards - RoHS Compliance Status	CM
Buy American Compliant	No
EU RoHS Indicator	Yes
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Run	350 kcmil 397 kcmil 400 kcmil 450 kcmil 477 kcmil 500 kcmil 550 kcmil 556 kcmil 600 kcmil 636 kcmil 650 kcmil 700 kcmil
Conductor - AL Str Tap Range	1/0 AWG-250 kcmil
Conductor - AL Str Tap	1/0 AWG 2/0 AWG 3/0 AWG 4/0 AWG 250 kcmil
Conductor Type	- ACSR C Str-Run - AL C Str-Run - ACSR C Str-Tap - AL C Str-Tap
Conductor - ACSR Str Run Range	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run	336.4 (18/1) Merlin kcmil 336.4 (26/7) Linnet kcmil 336.4 (30/7) Oriole kcmil 397.5 (18/1) Chickadee kcmil 397.5 (24/7) Brant kcmil

Conductor - ACSR Str Tap Range	
Conductor - ACSR Str Tap	

- 397.5 (26/7) Ibis kcmil
 - 397.5 (30/7) Larkspur kcmil
 - 477.0 (18/1) Pelican kcmil
 - 477.0 (24/7) Flicker kcmil
 - 477.0 (26/7) Hawk kcmil
 - 477. (30/7) Hen kcmil
 - 500.0 (30/7) Heron kcmil
 - 556.5 (24/7) Parakeet kcmil
 - 556.5 (26/7) Dove kcmil
 - 556.5 (30/7) Eagle kcmil
- 1 (6/1) Robin AWG-4/0 (6/1) Penguin AWG
- 1 (6/1) Robin AWG
 - 1/0 (6/1) Raven AWG
 - 2/0 (6/1) Quail AWG
 - 3/0 (6/1) Pigeon AWG
 - 4/0 (6/1) Penguin AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.53 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
Sub Brand	WEJTAP
UPC	781810874653
Type	Wejtap Connector
Material	Aluminum
UPC 12 Digit	781810874653
UPC 14 Digit GTIN	00781810874653

Logistics

Minimum Pack Quantity	10
Pallet Quantity	700
Carton Quantity	10



A Hubbell brand