



WCY80PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY80PB](#)



Wejtap connector installed with Yellow booster, .889-.1133 Run, .364-.608 (Tap), Quantity: 5 Connectors per Box

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	1-300
Conductor - AL Str Tap	• 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 266.8 • 300
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet

Conductor - ACSR Str Tap Range	• 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab • 605 (30/19) Teal • 636 (24/7) Rook • 636 (26/7) Grosbeak • 636 (30/19) Egret • 666.6 (24/7) Flamingo • 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard
Conductor - ACSR Str Tap	1 (6/1) Robin-266.8 (18/1) Waxwing
Conductor - ACSR Str Tap	• 1 (6/1) Robin • 1/0 (6/1) Raven • 2/0 (6/1) Quail • 3/0 (6/1) Pigeon • 4/0 (6/1) Penguin • 80 (8/1) Grouse • 101.8 (12/7) Petrel • 110.8 (12/7) Minorca • 134.6 (12/7) Leghorn • 159 (12/7) Guinea • 176.9 (12/7) Dotterel • 190.8 (12/7) Dorking • 203.2 (16/9) Brahma • 211.3 (12/7) Cochin • 266.8 (18/1) Waxwing

Configuration

Connector Type	Tap
----------------	-----

Dimensions


Dimension - G inch	1.79 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870747
Material	Aluminum

UPC 12 Digit	781810870747	Minimum Pack Quantity	5
UPC 14 Digit GTIN	00781810870747		

Logistics



Product Assets

[Catalog \[English\]](#)