



WCY82PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY82PB](#)



WEJTAP Connector, 1.133 - 0.889 (Run), 0.436 - 0.324 (Tap),
With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Run	• 556.5 • 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	2-3/0
Conductor - AL Str Tap	• 2 • 1 • 1/0 • 2/0 • 3/0
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Run	• 477.0 (30/7) Hen • 556.5 (24/7) Parakeet • 556.5 (26/7) Dove

- 556.5 (30/7) Eagle
 - 605 (24/7) Peacock
 - 605 (26/7) Squab
 - 605 (30/19) Teal
 - 636 (24/7) Rook
 - 636 (26/7) Grosbeak
 - 636 (30/19) Egret
 - 666.6 (24/7) Flamingo
 - 715.5 (54/7) Crow
 - 715.5 (26/7) Starling
 - 715.5 (30/19) Redwing
 - 795 (54/7) Condor
 - 795 (26/7) Drake
 - 795 (30/19) Mallard
 - 2 (6/1) Sparrow-2/0 (6/1) Quail
- | | |
|--------------------------|---|
| Conductor - ACSR Str Tap | <ul style="list-style-type: none">• 2 (6/1) Sparrow• 2 (7/1) Sparate• 1 (6/1) Robin• 1/0 (6/1) Raven• 2/0 (6/1) Quail |
|--------------------------|---|

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.79 in
Dimension - F Width Center to Center inch	3.5 in

General

Color	Yellow
Trade Name	WEJTAP™
UPC	781810870761
Material	Aluminum
UPC 12 Digit	781810870761
UPC 14 Digit GTIN	00781810870761

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[Catalog \[English\]](#)