


WCY89, WEJTAP Connector

By Burndy

Catalog # [WCY89](#)

Wejtap Connector With Power Booster Assembly, 12.63 IN L, 6.38 IN W, 0.893-1.250(Run), 0.923 -1.200(Tap), Installed With Yellow Booster



Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Application

For use in tap applications using large run and tap conductor sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range 600 kcmil-1000 kcmil
Conductor - AL Str Run

- 600 kcmil
- 636 kcmil
- 650 kcmil
- 700 kcmil
- 715 kcmil
- 750 kcmil
- 795 kcmil
- 800 kcmil
- 874 kcmil
- 900 kcmil
- 954 kcmil
- 1000 kcmil

Conductor - AL Str Tap Range 650 kcmil-1000 kcmil
Conductor - AL Str Tap

- 650 kcmil
- 700 kcmil
- 715 kcmil
- 750 kcmil
- 795 kcmil
- 800 kcmil
- 874 kcmil
- 900 kcmil
- 954 kcmil
- 1000 kcmil

Conductor - ACSR Str Run Range

Conductor - ACSR Str Run

556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil

- 556.5 (24/7) Parakeet kcmil
- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil
- 605 (24/7) Peacock kcmil
- 605 (26/7) Squab kcmil
- 605 (30/19) Teal kcmil
- 636 (24/7) Rook kcmil
- 636 (26/7) Grosbeak kcmil
- 636 (30/19) Egret kcmil
- 666.6 (24/7) Flamingo kcmil
- 715.5 (54/7) Crow kcmil
- 715.5 (24/7) Stilt kcmil
- 715.5 (26/7) Starling kcmil
- 715.5 (30/19) Redwing kcmil
- 795 (54/7) Condor kcmil
- 795 (26/7) Drake kcmil
- 795 (30/19) Mallard kcmil
- 874.5 (54/7) Crane kcmil
- 900 (54/7) Canary kcmil
- 954 (45/7) Rail kcmil
- 954 (54/7) Cardinal kcmil
- 1033.5 (45/7) Ortolan kcmil
- 1033.5 (54/7) Curlew kcmil

Conductor - ACSR Str Tap Range

Conductor - ACSR Str Tap

556.5 (26/7) Dove kcmil-954 (54/7) Cardinal kcmil

- 556.5 (26/7) Dove kcmil
- 556.5 (30/7) Eagle kcmil
- 605 (24/7) Peacock kcmil
- 605 (26/7) Squab kcmil
- 605 (30/19) Teal kcmil
- 636 (24/7) Rook kcmil
- 636 (26/7) Grosbeak kcmil
- 636 (30/19) Egret kcmil
- 666.6 (24/7) Flamingo kcmil
- 715.5 (54/7) Crow kcmil
- 715.5 (24/7) Stilt kcmil
- 715.5 (26/7) Starling kcmil
- 715.5 (30/19) Redwing kcmil
- 795 (54/7) Condor kcmil
- 795 (26/7) Drake kcmil
- 795 (30/19) Mallard kcmil
- 874.5 (54/7) Crane kcmil
- 900 (54/7) Canary kcmil
- 954 (45/7) Rail kcmil
- 954 (54/7) Cardinal kcmil

Configuration

Connector TypeTap

Dimensions

Dimension - G inch1.97 in
Package Height0.000 in
Package Weight0.000 lb.
Package Length0.000 in
Dimension - F Width Center to Center inch3.5 in
Package Width0.000 in

General

Trade NameWEJTAP™



A Hubbell brand

Sub BrandWEJTAP
UPC781810875858
TypeWejtap Connector
MaterialAluminum
UPC 12 Digit781810875858
UPC 14 Digit GTIN00781810875858

Logistics

Minimum Pack Quantity1
Pallet Quantity350
Carton Quantity5

Product Assets

[Catalog \[English\]](#)