



WCY89PB, WEJTAP Connector, Booster Included

By Burndy
Catalog # [WCY89PB](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 1.200 - 0.923 (Tap),
With Yellow Power Booster Assembly

Features

- WEJTAP Connector
- Yellow Power Booster Included

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600 kcmil-1000 kcmil
Conductor - AL Str Run	• 600 kcmil • 636 kcmil • 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - AL Str Tap Range	650 kcmil-1000 kcmil
Conductor - AL Str Tap	• 650 kcmil • 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet kcmil-1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet kcmil

	• 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil • 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil • 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil • 795 (30/19) Mallard kcmil • 874.5 (54/7) Crane kcmil • 900 (54/7) Canary kcmil • 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil • 1033.5 (45/7) Ortolan kcmil • 1033.5 (54/7) Curlew kcmil
Conductor - ACSR Str Tap Range	556.5 (26/7) Dove kcmil-954 (54/7) Cardinal kcmil
Conductor - ACSR Str Tap	• 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil • 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil • 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil • 795 (30/19) Mallard kcmil • 874.5 (54/7) Crane kcmil • 900 (54/7) Canary kcmil • 954 (45/7) Rail kcmil • 954 (54/7) Cardinal kcmil

Configuration

Connector Type	Tap	UPC	781810870839
		Material	Aluminum
Dimensions		UPC 12 Digit	781810870839
Dimension - G inch	1.97 in	UPC 14 Digit GTIN	00781810870839
Dimension - F Width Center to Center inch	3.5 in		
General		Logistics	
Color	Yellow	Minimum Pack Quantity	1
Trade Name	WEJTAP™	Product Assets	
 A Hubbell brand		Catalog [English]	
		© 2026 Hubbell Incorporated. All rights reserved BRDY-WCY89PB-SPEC-EN REV 5/2026	