



WCY95, WEJTAP Connector

By Burndy
Catalog # [WCY95](#)



Wejtap Assembly, 1.250-0.893 (Run), 0.722-0.525 (Tap), Installed
With yellow Booster

Features

- WEJTAP Connector
- Installed with Yellow Power Booster

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - AL Str Run Range	600-1000
Conductor - AL Str Run	• 600 • 636 • 650 • 700 • 715.5 • 750 • 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Tap Range	4/0-350
Conductor - AL Str Tap	• 4/0 • 250 • 266.8 • 300 • 336.4 • 350
Conductor Type	• ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet-1033.5 (54/7) Curlew
Conductor - ACSR Str Run	• 556.5 (24/7) Parakeet • 556.5 (26/7) Dove • 556.5 (30/7) Eagle • 605 (24/7) Peacock • 605 (26/7) Squab • 605 (30/19) Teal • 636 (24/7) Rook • 636 (26/7) Grosbeak • 636 (30/19) Egret

Conductor - ACSR Str Tap Range	4/0 (6/1) Penquin-336.4 (26/7) Linne
Conductor - ACSR Str Tap	• 4/0 (6/1) Penquin • 80 (8/1) Grouse • 101.8 (12/7) Petrel • 110.8 (12/7) Minorca • 134.6 (12/7) Leghorn • 159 (12/7) Guinea • 176.9 (12/7) Dotterel • 190.8 (12/7) Dorking • 203.2 (16/9) Brahma • 211.3 (12/7) Cochin • 266.8 (18/1) Waxwing • 266.8 (26/7) Owl • 266.8 (26/7) Partridge • 300.0 (26/7) Ostrich • 336.4 (18/1) Merlin • 336.4 (26/7) Linne

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - G inch	1.96 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	3.5 in
Package Width	0.000 in

General

Trade Name	WEJTAP™
UPC	781810876152
Material	Aluminum

UPC 12 Digit	781810876152	Pallet Quantity	350
UPC 14 Digit GTIN	00781810876152	Carton Quantity	5

Logistics

Minimum Pack Quantity 5



A Hubbell brand

Product Assets

[Catalog \[English\]](#)