



## WCY95PB, WEJTAP Connector, Booster Included

By Burndy  
Catalog # [WCY95PB](#)



WEJTAP Connector, 1.250 - 0.893 (Run), 0.722 - 0.525 (Tap),  
With Yellow Power Booster Assembly

### Features

- WEJTAP Connector
- Yellow Power Booster Included

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | NC |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

Conductor - AL Str Run Range 600-1000

Conductor - AL Str Run

- 600
- 636
- 650
- 700
- 715.5
- 750
- 795.5
- 800
- 874.5
- 900
- 954
- 1000

Conductor - AL Str Tap Range 4/0-350

Conductor - AL Str Tap

- 4/0
- 250
- 266.8
- 300
- 336.4
- 350

Conductor Type

- ACSR C Str-Run
- AL C Str-Run
- ACSR C Str-Tap
- AL C Str-Tap

Conductor - ACSR Str Run Range 556.5 (24/7) Parakeet-1033.5 (54/7) Curlew

Conductor - ACSR Str Run

- 556.5 (24/7) Parakeet
- 556.5 (26/7) Dove
- 556.5 (30/7) Eagle
- 605 (24/7) Peacock
- 605 (26/7) Squab

Conductor - ACSR Str Tap Range

Conductor - ACSR Str Tap

- 605 (30/19) Teal
- 636 (24/7) Rook
- 636 (26/7) Grosbeak
- 636 (30/19) Egret
- 666.6 (24/7) Flamingo
- 715.5 (54/7) Crow
- 715.5 (26/7) Starling
- 715.5 (30/19) Redwing
- 795 (54/7) Condor
- 795 (26/7) Drake
- 795 (30/19) Mallard
- 874.5 (54/7) Crane
- 900 (54/7) Canary
- 954 (54/7) Cardinal
- 1033.5 (54/7) Curlew

4/0 (6/1) Penquin-336.4 (26/7) Linne

- 4/0 (6/1) Penquin
- 80 (8/1) Grouse
- 101.8 (12/7) Petrel
- 110.8 (12/7) Minorca
- 134.6 (12/7) Leghorn
- 159 (12/7) Guinea
- 176.9 (12/7) Dotterel
- 190.8 (12/7) Dorking
- 203.2 (16/9) Brahma
- 211.3 (12/7) Cochin
- 266.8 (18/1) Waxwing
- 266.8 (26/7) Owl
- 266.8 (26/7) Partridge
- 300.0 (26/7) Ostrich
- 336.4 (18/1) Merlin
- 336.4 (26/7) Linne

### Dimensions

|                                           |         |
|-------------------------------------------|---------|
| Dimension - G inch                        | 1.96 in |
| Dimension - F Width Center to Center inch | 3.5 in  |

### General

|                   |                |
|-------------------|----------------|
| Color             | Yellow         |
| Trade Name        | WEJTAP™        |
| UPC               | 781810870891   |
| Material          | Aluminum       |
| UPC 12 Digit      | 781810870891   |
| UPC 14 Digit GTIN | 00781810870891 |

Minimum Pack Quantity 5

[Catalog \[English\]](#)



A Hubbell brand