



YA25L4TCG1, Comp. Term., Cu, Std Barrel, 4-Hole Split Pad

By Burndy

Catalog # [YA25L4TCG1](#)



Copper Compression Terminal, 1/0 AWG Cu, 4-Hole Split Pad, 1/4" Stud, .62" Spacing (.75" between tongues), Standard Barrel, Tin Plated

Features

- Compression Terminal, Split Pad, 4-Hole

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1/0 AWG
Conductor Size	1/0 AWG
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	1/0 AWG

Configuration

Physical Attribute - Number of Holes	4
Number of Pad Holes	4
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/4

Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	0.75 in
Package Width	0.000 in
Dimension - L Length Overall mm	77 mm
Dimension - Outside Diameter inch	0.51 in
Dimension - Hole Size mm	6.9 mm
Dimension - Hole Size inch	0.27
Dimension - Strip Length inch	15/16
Dimension - Stud Size inch	1/4
Dimension - Stud Size fraction	1/4
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	7/8 in
Dimension - Z inch	0.20 in
Dimension - B Length inch	0.88 in
Dimension - D inch	1.13 in
Dimension - N inch	0.31 in
Dimension - Bolt Size inch	0.25
Dimension - Length Overall inch	3.05 in

General

Trade Name	HYLUG™
Die Index	12
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Pink
Sub Brand	HYLUG
UPC	781810125854
Type	Standard Barrel, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810125854
UPC 14 Digit GTIN	00781810125854

Logistics

Pallet Quantity	11520
-----------------	-------



A Hubbell brand