



# YA34A13, Aluminum Stackable Terminal, Straight Lug

By Burndy  
Catalog # [YA34A13](#)

Aluminum Stackable Terminal- Straight Lug, 500 Kcmil, Pink,1 hole,Tin - Electro Plated



### Features

- Aluminum Stackable Terminal - Straight Lug
- 1-Hole, Tin Plated

### Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliance   | CM  |
| Status                        |     |
| Certification - cULus         | No  |
| UL Listed                     | Yes |
| Certification - CSA Approved  | No  |

### Conductor

|                               |           |
|-------------------------------|-----------|
| Conductor - AL Str Size       | 500 kcmil |
| Conductor - AL Str Size Range | 500 kcmil |
| Conductor - Copper Str Size   | 500 kcmil |

### Configuration

|                                                |          |
|------------------------------------------------|----------|
| Physical Attribute - Number of Crimps Required | 2        |
| Physical Attribute - Number of Holes           | 2        |
| Connector Type                                 | Terminal |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - Pad Width inch        | 1.62 in  |
| Dimension - Hole Size fraction    | 5/9      |
| Physical Attribute - Tongue Angle | Straight |
| Dimension - Height inch           | 0.98 in  |
| Dimension - Height fraction       | 49/50 in |

|                                   |         |
|-----------------------------------|---------|
| Dimension - P inch                | 3.65 in |
| Dimension - L Length Overall mm   | 188 mm  |
| Dimension - B Length inch         | 2.34 in |
| Dimension - Outside Diameter inch | 1.32 in |
| Dimension - Hole Size inch        | 0.56 in |
| Dimension - Length Overall inch   | 7.42 in |
| Dimension - Strip Length inch     | 2-5/8   |

### General

|                        |                      |
|------------------------|----------------------|
| Feature - Barrel Style | Chamfered            |
| Plated                 | Y                    |
| Color Code             | Pink                 |
| Trade Name             | HYLUG™               |
| Die Index              | 300                  |
| UPC                    | 781810130728         |
| Material               | Aluminum             |
| Plating Type           | Tin - Electro Plated |
| UPC 12 Digit           | 781810130728         |
| UPC 14 Digit GTIN      | 00781810130728       |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2880 |
| Carton Quantity       | 12   |

### Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)