

YAD186, Ring Terminal, 22-18 AWG, 1-Hole, #4-6 Stud

By Burndy
Catalog # [YAD186](#)

Uninsulated Ring Terminal For 22 - 18 AWG, #4-6 Stud, Tin Plated,
Brazen Seam, Bulk Package



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazen seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hold for an easy visual check of wire insertion
- Long neck terminal permits easy bending and stacking of several terminals on a common stud

Application

For control wiring and other standard duty applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	22 AWG - 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Pad Width inch	0.26 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/50
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	17 mm
Dimension - Hole Size inch	0.14 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Bolt Size fraction	#4 - #6
Dimension - Z inch	0.24 in
Dimension - Length Overall inch	0.65 in

General

Product Family	COMPRESSION
Trade Name	HYLUG™
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Yes
Physical Attribute - Tongue Type	Ring
Sub Brand	HYLUG
Product Type	Terminal
UPC	781810806197
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810806197
UPC 14 Digit GTIN	00781810806197

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)