



YA39A1N131TD12E, 750 kcmil AL, 1-Hole, 1/2" Stud

By Burndy
Catalog # [YA39A1N131TD12E](#)

750 kcmil, AL, 1-Hole, 1/2" Stud, AL9CU, Tin Plated, Prefilled with oxide inhibitor, End Cap

Features

- UL486A-486B Listed and CSA Certified
- Aluminum terminals are dual rated to accommodate both copper and aluminum wire and are indicated with AL-CU on the connector - AL9CU is UL Listed 90°C, up to 35kV, AL7CU is UL Listed 75°C, up to 35kV
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damage of the wire strands during insertion
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX Type A13 oxide inhibitor
- Color coded end caps are factory inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel
- Aluminum oxidation is not easily detected but causes resistance in a connection, it is imperative the proper preparation takes place prior to making an aluminum-to-aluminum connection

Application

Wire Termination

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	750 KCMIL
Conductor - Material	ALUMINUM / COPPER
Wire Size	750 KCMIL
Conductor - AL Str Size	700 KCMIL-750 KCMIL
Conductor - AL Str Size Range	750 kcmil
Conductor Type	CODE



Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Str Size	• 700 KCMIL • 750 KCMIL

Configuration

Connector Type	DUAL RATED
----------------	------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Bolt Size fraction	1/2
Physical Attribute - Tongue Angle	Straight
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.5
Dimension - Hole Size inch	0.56
Dimension - Stud Size fraction	1/2

General

Color Code	Pink
Trade Name	HYLUG™
Sub Brand	TERMINALS, HYLUG
Die Index	300
UPC	781810281321
Type	YA-E
Material	ALUMINUM
Finish Type	Tin-Plated

Logistics

Pallet Quantity	4640
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)