




YAE22N66F, Nylon Fork Terminal For 26 - 20 AWG

By Burndy
Catalog # [YAE22N66F](#)

Nylon Fork Terminal For 26 - 20 AWG



Features

- Multi-finger insulation grip provides superior insulation holding characteristics, especially on EPR and other elastic-type insulations
- Brazed seam provides a stronger, more durable termination
- Manufactured of pure electrolytic copper for maximum conductivity, low resistance, and ductility for excellent crimp forming properties
- Deep V groove, inner barrel serrations for optimum conductivity, reliability and holding power
- Smooth funnel entry for easy wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
Industry Standard(s)	Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Aircraft Size	• AN 26 • AN 22 • AN 20
Conductor Size	26 - 20 AWG
Conductor - Copper Str Size	20 AWG
Conductor - Copper Str Size Range	24 AWG - 20 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	10/91 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.11 in
Dimension - Z inch	0.27 in
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.15 in
Dimension - Strip Length inch	5/32 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Length Overall inch	0.8 in
Dimension - N inch	0.12 in

General

Insulation Type	Nylon
Color Code	Amber
Physical Attribute - Tongue Type	Fork
Trade Name	INSULUG™
Plated	Y
Insulation	Y
UPC 12 Digit	781810804049
UPC 14 Digit GTIN	00781810804049
Material	Copper
Plating Type	Tin
UPC	781810804049

Logistics

Minimum Pack Quantity	1000
Packaging Type	Bulk
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)