



YAD1810F, Uninsulated Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YAD1810F](#)

Uninsulated Fork Terminal For 22 - 18 AWG



Features

- Constructed of pure electrolytic copper for maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Long brazed seam barrel and deep V groove inner serrations provide optimum conductivity reliability and holding power after crimping
- Electro-tin plating to provide durable, long-lasting corrosion resistance
- Wire range is clearly marked on terminal for easy identification
- Inspection hole for an easy visual check of wire insertion
- Long nect terminal permits easy bending and stacking of several terminals on a common stud

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	• 22 AWG • 20 AWG • 18 AWG
Conductor - Copper Solid Size Range	22 AWG-18 AWG
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	• 22 AWG • 20 AWG • 18 AWG
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	CU C Solid-Size, CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.28 in
Dimension - L Length Overall mm	19 mm
Dimension - Pad Width inch	0.37 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size inch	0.20 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	• #8 • #9 • #10
Dimension - Length Overall inch	0.73 in

General

Physical Attribute - Tongue Type	Fork
Trade Name	HYLUG™
Plated	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Type	Fork Tongue
UPC 12 Digit	781810806227
UPC 14 Digit GTIN	00781810806227
Material	Copper
Plating Type	Tin
UPC	781810806227

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)