



YAEV10T26, Nylon Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YAEV10T26](#)



Nylon Ring Terminal For 12 - 10 AWG

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 12 • AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor Size	12 - 10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	3/10 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.30 in
Dimension - Outside Diameter inch	0.28 in
Dimension - Z inch	0.27 in
Dimension - P inch	0.09 in
Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Bolt Size fraction	#8 - #10
Dimension - Hole Size inch	0.20 in
Dimension - Stud Size inch	• #8 • #10
Dimension - Length Overall inch	1.11 in
Dimension - N inch	0.16 in

General

Insulation Type	Nylon
Color Code	Yellow
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG™
Plated	Y
Insulation	Y
UPC 12 Digit	781810050972
UPC 14 Digit GTIN	00781810050972
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810050972

Logistics

Minimum Pack Quantity	500
Carton Quantity	500
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand