



YAEV14T2, Nylon Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YAEV14T2](#)



Nylon Ring Terminal For 16 - 14 AWG

Features

- Double thick tongue for maximum reliability and electrical capacity plus an extra strong terminal tongue
- Manufactured from one-piece pure electrolytic copper — high conductivity, low resistance with no seams to split plus ductility for excellent crimp forming properties
- Electro-tin plated to provide long-lasting corrosion resistance
- Nylon insulation is locked in place — Insulation will not move or twist off
- 600 volt nylon insulation providing high dielectric strength and stability in demanding oily environmental conditions
- Color Coded providing quick, easy wire size connector selection

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	• UL486 • Military Specified (Mil-Spec)
Certification - CSA Approved	No
UL Listed	Yes

Conductor

Conductor - Copper Str Aircraft Size	• AN 18 • AN 16 • AN 14
Conductor - Copper Str Aircraft Size Range	AN 18-AN 14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	20AWG ,18 AWG, 16 AWG, 14 AWG
Conductor - Copper Str Size Range	20 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Width inch	0.10 in
Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.32 in
Dimension - Pad Width inch	0.38 in
Package Height	0.000 in
Dimension - Hole Size fraction	10/37
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Stud Size inch	1/4
Dimension - N inch	0.26 in

General

Sub Brand	INSULUG
Insulation Type	Nylon
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Trade Name	INSULUG™
Plated	Y
Construction Material - Main Insulation	Copper Y
Type	YAEV
UPC 12 Digit	781810082218
UPC 14 Digit GTIN	00781810082218
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC	781810082218

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999



A Hubbell brand